

Product Information - SV LIFE SCIENCES

SV Pressure Transmitter

Introduction

The Anderson-Negele SV Life Sciences Series Pressure Transmitter offers not only a new low profile design, but may be ordered with built-in LCD indication. The unit meets all life sciences requirements for performance, finish and cleanability. It is designed and manufactured to withstand the harsh process and sterilization conditions encountered in the Life Sciences industry.

Its one-piece stainless steel package design incorporates a transducer and electronic circuitry to convert pressure and/or vacuum to a proportional 4-20 mA signal. The wide variety of fittings and ranges provide flexibility in specifying the best transmitter for any application. The unit is designed to operate at high process temperatures and withstand CIP/SIP conditions.

All units are supplied factory calibrated to standard or custom ranges. For field maintenance, non-interactive zero, and span adjustments, as well as field accessible test points are provided. The optional LCD cap mounted display can be scaled to match actual process units, 0-100% of full scale, or 4-20 mA. This useful feature provides indication directly at the process, in addition to the standard 4-20 mA output. Permanently marked tagging is provided at no extra charge. In addition the SV complies with Class 1, Div. 1, Groups A, B, C and D for intrinsically safe apparatus. Units are supplied with certificates of calibration.



Specifications

Excitation: 9-32 VDC (Absolute), 24 VDC Nominal Housing Material:

regulated or unregulated

14-37 VDC (Absolute) with display

Output: 4-20 mA DC

Loop Resistance: 0-750 ohms at 24 VDC

0-1050 ohms at 30 VDC

Indication: Optional, 3 1/2 digit, .5" high LCD, cap

mounted

Accuracy: ± 0.5% of span, full scale, for standard

ranges except those below

0-50 psig (±1.0% full scale. All vacuum/

pressure ranges and PSIA ranges are ±1.0%)

Over-Range Rating: 2 times base range

Stability: ± 0.3% of calibrated range / 6 months

Zero and Span Adjustments: ± 10% of range

Repeatability: ± 0.3% Hysteresis: ± 0.1% Linearity: ± 0.1% **Process Temperature Range:**

20° to 275°F (Up to 325°F if horizontal

mount)

Process Temperature Effect: ± 0.1 psig/5.5°C (10°F)

Ambient Temp. Operating Range:

-17.8° to 48.9°C (0° to 120°F)

Storage Temperature: -40° to 65° C (-40° to 149° F)

Direct connection Mounting: 304 Stainless Steel

NEMA 4X, IP66 **Housing Ratings:**

Wetted Parts: 316L Stainless Steel standard; Hasteloy "C"

diaphragm optional

Actuating Fill: 100% mineral oil. Meets FDA requirements

(21 CFR, 172.878 and 178.3620(a))

Surface Finish (wettable parts):

Ra max = 8 microinches (.2 microns)

electropolished

Recommended Cable: 18-24 AWG, foil shielded, and PVC coated.

(3/16 - 1/4 OD insulation)

Wiring Connection: Screw Terminal; Accessible via removable

screw cap conduit housing

UL Approved; Complies with Class 1, Div. 1, Approvals:

Grps. A-D for intrinsically safe apparatus

Standard: Designed and manufactured to sound

engineering practices in accordance with

Article 3.3 of the PED 97/23/EC

CSA B51-03


CRN# CSA0F9754.5C

Response Time: 200 µSec

* Specifications are subject to change without notice.



Order Information



SPECIFY TAGGING INFORMATION TO BE PERMANENTLY MARKED, IF APPLICABLE

