



Centrifugal Pump GM (GHC-00)

Pos.	Qty.	Description	
1	1	Motor T.E.F.C. 0.25 - 0.5 hp/1800RPM	
	1	Motor T.E.F.C. 0.25 - 1.0 hp/3600RPM	
2	4	Screw	9611-99-1495
3	4	Washer	41381
4	1	Bracket	31456-0101-1
5	1	Thrower	31437-0038-1
6	1	Set screw	31456-0111-1
7a	1	Pump Shaft-Thd.	31456-0098-1
7b	1	Pump Shaft-Thd.	31456-0092-1
8	1	Backplate-Ind.	31456-0035-1
	1	Backplate 3A	31456-0035-2
9a	1	Impeller, 095 (T316) Thd.	31457-0016-8
9b	1	Impeller, 095 (Polyamid) Std.	31456-0009-2
10	1	Joint Ring, EPDM (Std.)	2234121-75
	1	Joint Ring, Viton	223412-76
	1	Joint Ring, PTFE	31456-0060-1
11	1	Pump Casing-GC Ind	31456-0133-3
	1	Pump Casing-GC 3A	31456-0091-2
	1	Pump Casing-Bevel Seat 3A	31456-0091-3
12	2	Stud Bolt	31457-0051-4
13	2	Wing Nut	31336-0143-2
14	2	Collet	31456-0054-1
22	1	Nut	31437-0120-1
30	1	Frame	31456-0112-1
31	3	Nut	9611-99-1829
32	3	Washer	31460-0104-1
33	3	Leg	31460-0112-1
Shaft seal, compl., Nitrile (Std.)			31437-0213-7
19	1	Spring	104154
20	1	Spacer	31437-0212-1
21	1	Washer	104125
23	1	Stationary seal ring	31437-0119-2
24	1	O-ring	31439-0168-1
25	1	Rotating seal ring	31437-0211-1
26	1	Packing	31437-0121-1
Shaft seal, compl., EPDM			31437-0213-6
19	1	Spring	104154
20	1	Spacer	31437-0212-1
21	1	Washer	104125
23	1	Stationary seal ring	9612-3755-01
24	1	O-ring	31439-0168-4
25	1	Rotating seal ring	31437-0211-1
26	1	Packing	31437-0121-3
Shaft seal, compl., Viton			31437-0218-8
19	1	Spring	104154
20	1	Spacer	31437-0212-1
21	1	Washer	104125
23	1	Stationary seal ring	9612-3758-01
24	1	O-ring	31439-0168-5
26	1	Packing	31437-0121-3
Shaft seal, compl., Teflon			31437-0213-9
19	1	Spring	104154
20	1	Spacer	31437-0212-1
21	1	Washer	104126
23	1	Stationary seal ring	9612-3758-01
24	1	O-ring	31439-0168-3
25	1	Rotating seal ring	31437-0211-1
26	1	Packing	31437-0121-3
For abrasive liquids			
23	1	Stationary seal ring with silicon carbide	31437-0225-1
25*	1	Rotating seal ring with silicon carbide	31437-0211-4

*Sometimes reduced impeller dimensions.
Check the dimensions of the original impeller.
Recommended spare parts: pos. 10 and complete shaft seal

*The rotating seal ring with silicon carbide must not be used with at stationary seal ring of stainless steel.



CSI

CONTACT CSI FOR MORE INFORMATION | CSIDESIGNS.COM | SALES@CSIDESIGNS.COM | 417.831.1411